

# PN7140 Solvent Organizer



Technical specifications are subject to change without further notice.

**Solvent Organizer for Efficient  
and Safe Liquid Handling!**

[www.postnova.com](http://www.postnova.com)

# Specifications

## Working Principle:

By the use of an special collection tray

## Flow Rate:

Max. 10 mL/min for each channel.

## Channels:

Standard: 2, 3 or 4 channels.

## Parts which come in contact with the solvent:

PTFE for organic solvents  
PEEK for aqueous solvents

## Channel Volume:

0.85 mL per channel.

## Error Message:

Visually over main on/off LED line integrated outside into the system cover.

## Dimensions:

Width x Height x Length  
285 x 65 x 420 mm

## Weight:

3 kg



## Postnova Analytics GmbH

Max-Planck-Str. 14  
86899 Landsberg am Lech/Germany  
Tel. : +49.8191.428-181  
Fax : +49.8191.428-175

## Postnova Analytics Inc.

230 South, 500 East, Suite # 120  
84102 Salt Lake City, UT/USA  
Tel. : +1.801.521-2004  
Fax : +1.801.521-2884

email : [info@postnova.com](mailto:info@postnova.com)  
web : [www.postnova.com](http://www.postnova.com)

# Solvent Organizer PN7140

## Operation principle

Holder for bottles and possibility of direct connection of up to 4 solvents lines via the PEEK connector block.

## Available versions

4-Channel Version; Part#: S-REA-7140-001

Special versions maybe provided by Postnova as well. Please inquire for possible options, which will depend on the requested customer application.

